

RENZMANN

Washing machine for mixing vessels



RIO-VsmarT

Cleaning with solvent
or
aqueous media



For vessels with outlet

EFFICIENT CLEANING



► Clean containers = less downtime

EASY HANDLING



► Short and reliable washing cycles

HIGH-QUALITY



► High-end components and sturdy construction

TECHNICAL DATA

Container Ø inside/outside max. [mm]
Container Ø inside min. [mm]
Container height inside [mm]
Rim height above floor [mm]
Dimensions W x D x H [mm]

Size 1

1200 / 1300
600
700 - 1350
max. 1500
1800 x 2750 x 3935

Size 2

1500 / 1550
750
700 - 1350
max. 1500
1800 x 2750 x 3935



Sustainability First!
Combine washing and
distilling



Why a RIO-VsmarT?



EFFICIENT CLEANING:

Efficient internal cleaning of round containers with centrifugal brush.
Washing with recirculating washing solvent and rinsing with clean solvent.



EASY HANDLING:

Automatic washing program and pneumatical lifting and lowering of brush and lid.



SAFE USE:

Conductive brushes with type examination. Explosion protection according to ATEX, category 1 (with type examination) for zone 0 inside, category 2 for zone 1 outside the machine.



ROBUST DESIGN:

High-quality components like pumps and ventilators.
Long life cycle with regular maintenance.



Before/ After



Partner with our **multidisciplinary experts** for **tailored advice** and **worldwide customer care!**

Cleaning and Distillation Trials
technikum@renzmann.com

Consultation and Sales
sales@renzmann.com

Service and Maintenance
service@renzmann.com